



VU12ET

Encl.,Volta,flush,1x12MOD,IP30,Version Spain,transparent door

Technical Features

Voltage

Nominal voltage 400 - 400 V

Installation, mounting

Suitable for outdoor usage No

Mounting on Flush mounting

Electric current

Rated current 63 A

Power

Maximum power loss per cabinet at $\Delta T=20K$ 12 W

Equipment

Number of rails 1

Number of rows 1

Number of section in width 1

With lock No

Has neutral terminal block No

Capacity

Number of modules 12

Number of half modules terminals per rail 24

Functions

With conduit inlets Yes

Dimensions

Height 356 mm

Width 348 mm

Depth 94.50 mm

Built-in height 340 mm

Built-in width 335 mm

Cover, door

Number of cabinet doors 1

Dimensions

Built-in depth 90 mm

Cover, door

Number of locks 0

Dimensions

Number of width units 12

Cover, door

Door/cover is transparent Yes

Connectivity

Mounting type Screw mounting

Materials

Material Plastic

RAL code 9010

Colour Pure white

Equipment

Has earthing terminal block Yes

Has mounting plate No

Materials

Ultraviolet-resistant	Yes
-----------------------	-----

Safety

Protection class	Isolation class II
------------------	--------------------

Ingress Protection (IP) class	IP30
-------------------------------	------

Locking type	Snap on lock Without lock
--------------	------------------------------

Glow wire test	650 °C
----------------	--------

Sustainability

RoHS conform	Yes
--------------	-----
