



VM402HK

Consumer unit, Design 30, 2way, 40A, 30mA, RCCB incomer, KO

Technical Features

Installation, mounting

Mounting on Surface mounting

Functions

Has protection main switch Yes

Capacity

Number of modules 2

Electric current

Rated current 40 A

Dimensions

Depth 102 mm

Height 240 mm

Width 149 mm

Number of width units 2

Cover, door

Interlockable Yes

Door/cover is transparent No

Materials

RAL code 7035

Colour Light grey

Material Steel

Connection

Number of accessible phases 1

Scope of delivery

Number of RCCB in enclosure 1

Equipment

Number of rows 1

Number of rails 1

With socket outlet No

Safety

Ingress Protection (IP) class IP2XC

Number of earth leakage switches 300 mA 0

Sustainability

RoHS conform Yes