



JK2B24S2

Technical Features

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Electric current

Breaking and opening capacity ldm	0 kA
-----------------------------------	------

Equipment

Has mounting plate	No
--------------------	----

Equipped with switch	No switch
----------------------	-----------

Number of switches	0
--------------------	---

Type of busbar chassis	Fixed load chassis
------------------------	--------------------

Capacity

Number of modules	24
-------------------	----

Dimensions

Height	1195 mm
--------	---------

Width	445 mm
-------	--------

Depth	125 mm
-------	--------

Cover, door

Number of cabinet doors	1
-------------------------	---

Door/cover is transparent	No
---------------------------	----

Materials

Material	Steel
----------	-------

RAL code	9002
----------	------

Colour	Grey white
--------	------------

Safety

Protection class	Isolation class I
------------------	-------------------

Impact resistance IK	IK05
----------------------	------

Ingress Protection (IP) class	IP41
-------------------------------	------

Locking type	Special tool Without lock
--------------	------------------------------

Architecture

Number of poles	72
-----------------	----

Sustainability

REACH-SVHC free	Yes
-----------------	-----

RoHS conform	Yes
--------------	-----