



FU42GN

Enclosure, NewVegaD, 837x550x182mm, 96 modules, flush-mounted, empty

**Technical Features**

**Dimensions**

Height	837 mm
Width	600 mm
Depth	182 mm
Thickness of sidewall	1 mm

**Safety**

Ingress Protection (IP) class	IP30
Protection class	Isolation class II
Locking type	Without lock
Impact resistance IK	IK07

**Equipment**

Number of section in width	2
Number of flange plate openings	2

**Installation, mounting**

Mounting on	Flush mounting
Suitable for outdoor usage	No

**Materials**

Colour	Pure white
RAL code	9010
Treatment	Powder coated
Material	Metal Plastic

**Equipment**

Number of rows	4
----------------	---

**Cover, door**

Number of cabinet doors	0
Door/cover is transparent	No

**Electric current**

Rated current	160 A
---------------	-------

**Sustainability**

RoHS conform	Yes
--------------	-----