



FU42GN

Enclosure, NewVegaD, 837x550x182mm, 96 modules, flush-mounted, empty

Technical Features

Dimensions

Height	837 mm
Width	600 mm
Depth	182 mm
Thickness of sidewall	1 mm

Safety

Ingress Protection (IP) class	IP30
Protection class	Isolation class II
Locking type	Without lock
Impact resistance IK	IK07

Equipment

Number of section in width	2
Number of flange plate openings	2

Installation, mounting

Mounting on	Flush mounting
Suitable for outdoor usage	No

Materials

Colour	Pure white
RAL code	9010
Treatment	Powder coated
Material	Metal Plastic

Equipment

Number of rows	4
----------------	---

Cover, door

Number of cabinet doors	0
Door/cover is transparent	No

Electric current

Rated current	160 A
---------------	-------

Sustainability

RoHS conform	Yes
--------------	-----