

Insulated busbar 3P 80A prong 10mm² 12M

Technical Features

Electric current

Rated current	80 A
---------------	------

Architecture

Number of poles	3
-----------------	---

Dimensions

Length	210 mm
--------	--------

Voltage

Rated impulse withstand voltage Uimp	4000 V
--------------------------------------	--------

Rated operational voltage Ue	230 - 400 V
------------------------------	-------------

Connection

Cross-section rigid conductor	16 mm ²
-------------------------------	--------------------

Connector/plug type	Phase busbar with pin
---------------------	-----------------------

Capacity

Number of modules	12
-------------------	----

Sustainability

RoHS conform	Yes
--------------	-----