

Insulated busbar 3P 80A prong 10mm² 12M

Technical Features

Electric current	
Rated current	80 A
Architecture	
Number of poles	3
Dimensions	
Length	210 mm
Voltage	
Rated impulse withstand voltage Uimp	4000 V
Rated operational voltage Ue	230 - 400 V
Connection	
Cross-section rigid conductor	16 mm ²
Connector/plug type	Phase busbar with pin
Capacity	
Number of modules	12
Sustainability	
RoHS conform	Yes