



EG010



IP20



Daily time switch 1 channel, digital, 1 module

Technical Features

Voltage

Rated operational voltage U_e 230 - 230 V

Frequency

Frequency 50 - 50 Hz

Power

230 V incandescent and halogen lamp 1000 W

Functions

Power reserve in years 3 y
 With network synchronisation No
 With quartz synchronisation Yes
 Number of function channels 1

Equipment

Accuracy per day 60 s
 With impulse programme No
 Number of channels 1

Connection

Type of contacts 1x changeover

Settings

Daily programme Yes
 Weekly programme No
 Annual programme No

Use conditions

Operating temperature -10 - 50 °C

Connection

Cross-section flexible conductor 1 - 4 mm²
 Cross-section rigid conductor 1 - 4 mm²

Texts

Type of connection With screw terminals

Dimensions

Height 92 mm
 Width 18 mm
 Depth 64 mm

Main electrical attributes

Minimum interval between 2 switching times 1 min

Capacity

Number of modules 1