



EG010



Daily time switch 1 channel, digital, 1 module

Technical Features

Voltage

Rated operational voltage Ue	230 - 230 V
------------------------------	-------------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Power

230 V incandescent and halogen lamp	1000 W
-------------------------------------	--------

Functions

Power reserve in years	3 y
With network synchronisation	No
With quartz synchronisation	Yes
Number of function channels	1

Equipment

Accuracy per day	60 s
With impulse programme	No
Number of channels	1

Connection

Type of contacts	1x changeover
------------------	---------------

Settings

Daily programme	Yes
Weekly programme	No
Annual programme	No

Use conditions

Operating temperature	-10 - 50 °C
-----------------------	-------------

Connection

Cross-section flexible conductor	1 - 4 mm ²
Cross-section rigid conductor	1 - 4 mm ²

Texts

Type of connection	With screw terminals
--------------------	----------------------

Dimensions

Height	92 mm
Width	18 mm
Depth	64 mm

Main electrical attributes

Minimum interval between 2 switching times	1 min
--	-------

Capacity

Number of modules	1
-------------------	---