



75441326



KNX CO2 sensor w. humidity and temperature regulation, Q.x anthr. velvety, lacq.

Technical Features

Electric current

Bus current consumption data transfer	12,50 mA
---------------------------------------	----------

Functions

Parallel service possible	No
With local operation	No

Materials

Colour	Anthracite
RAL code	7021

Dimensions

Dimensions	70 x 70 mm
------------	------------

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Use conditions

Operating temperature	-5 - 45 °C
Energy efficiency class	IV (2%)

Voltage

Operating voltage over bus	21 - 32 V
----------------------------	-----------

Texts

Function	Binary input functions: Switching, dimming, blind, value transmitter, light scene extension unit Binary inputs can be blocked in operation
Temperature	An alarm is signalled when the dewpoint is reached in order to prevent the formation of mould e.g. on cooling ceilings or in winter gardens
Installation mode	Without spreader claws

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes