



75441329



KNX CO2 sensor with humidity and temperature regulation, Q.x polar white velvety

Technical Features

<b>Electric current</b>	
Bus current consumption data transfer	12,50 mA

<b>Functions</b>	
Parallel service possible	No
With local operation	No

<b>Materials</b>	
Colour	Polar white
RAL code	9010

<b>Dimensions</b>	
Dimensions	70 x 70 mm

<b>Safety</b>	
Ingress Protection (IP) class	IP20

<b>Use conditions</b>	
Operating temperature	-5 - 45 °C
Energy efficiency class	IV (2%)

<b>Voltage</b>	
Operating voltage over bus	21 - 32 V

<b>Texts</b>	
Function	Binary input functions: Switching, dimming, blind, value transmitter, light scene extension unit Binary inputs can be blocked in operation
Temperature	An alarm is signalled when the dewpoint is reached in order to prevent the formation of mould e.g. on cooling ceilings or in winter gardens
Installation mode	Without spreader claws

<b>Sustainability</b>	
REACH-SVHC free	Yes
RoHS conform	Yes