



50763505



**Technical Features**

**Electric current**

Momentary contact current	10 A
---------------------------	------

**Voltage**

Rated voltage	250 V
---------------	-------

**Architecture**

Control/operation element	Single rocker
Number of poles	1

**Materials**

Colour	Grey
Surface finish	Matt
Material	Thermoplastic
Treatment	Untreated
Transparent	No

**Dimensions**

Height	76 mm
Width	76 mm
Depth	61.50 mm
Built-in depth flush-mounted boxes	0 mm

**Installation, mounting**

Mounting on	Surface mounting
-------------	------------------

**Controls and indicators**

Number of buttons	1
Type of push button	Single push button
With feedback signal contact	No

**Safety**

Ingress Protection (IP) class	IP55
Impact resistance IK	IK05

**Accessories**

Has labelling field	No
---------------------	----

**Use conditions**

Operating temperature	-25 - 35 °C
-----------------------	-------------

**Texts**

Imprint	Without imprint
Lighting	With blue 230 V LED unit For lighting and monitoring circuit
Sealing	With full-face sealing on the rear side of housing for cable entry and surface adjustment on the backside
Terminal	With Wago clip-in 2-wire connection terminal for wiring With two clip-in places for Wago 2-wire connection terminals in the housing floor
Type of connection	With N-terminal With plug-in terminals