



WPSSU83FO

13A FCU Switched with Flex Outlet & Back Box with Knockouts

Technical Features

Installation, mounting

Mounting on Surface mounting

Voltage

Rated voltage 250 V

Frequency

Frequency 50 - 60 Hz

Materials

Colour Grey

Surface finish Glossy

Material Steel

Treatment Epoxy

Identification

Assembly arrangement Basic element with full cover plate

Connectivity

Mounting type Screw mounting

Controls and indicators

Number of buttons 1

Dimensions

Dimensions 86 x 86 mm

Safety

Ingress Protection (IP) class IP20

Electric current

Rated current 13 A

Texts

Installation mode For flush-mounted and hollow wall mounting

Lighting Without lighting (cannot be illuminated)

Switch mode 2-pole

Sustainability

REACH-SVHC free Yes

RoHS conform Yes