



JG220U

IP66 63A 2P UTILITY ISOLATOR

Technical Features

Architecture

Number of poles	2
Type of pole	1P+N

Electric current

Rated current	63 A
Acceptable current rating AC21 category A	63 A
Acceptable current rating AC22 category A	63 A

Voltage

Rated operational voltage Ue	250 - 250 V
------------------------------	-------------

Electric current

Rated short-circuit making capacity Icm under 240 V AC according to IEC 60947-3	0.75 kA
---	---------

Voltage

Rated insulation voltage Ui	250 V
-----------------------------	-------

Electric current

Rated short-time withstand current Icw t=1 S 220 - 240 V AC according to IEC 60947 - 3	0.75 kA
--	---------

Installation, mounting

Nominal tightening torque	2.50 - 2.50 Nm
---------------------------	----------------

Dimensions

Height	170 mm
Width	84 mm
Depth	87 mm

Safety

Ingress Protection (IP) class	IP66
-------------------------------	------

Use conditions

Operating temperature	-5 - 40 °C
-----------------------	------------

Connection

Cross-section rigid conductor	10 - 16 mm ²
-------------------------------	-------------------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Sustainability

RoHS conform	Yes
--------------	-----