



VP54G

Enclosure, Vector, Polycarbonate, plain door, 400x500x210 mm

**Technical Features**

**Installation, mounting**

Mounting on	Surface mounting
-------------	------------------

**Electric current**

Rated current	63 A
---------------	------

**Equipment**

Number of rows	3
With lock	Yes
Has neutral terminal block	No

**Capacity**

Number of modules	54
-------------------	----

**Dimensions**

Height	500 mm
Width	400 mm
Depth	210 mm

**Cover, door**

Number of cabinet doors	1
-------------------------	---

**Dimensions**

Built-in depth	210 mm
----------------	--------

**Cover, door**

Door/cover is transparent	No
---------------------------	----

**Materials**

Material	Polycarbonate (PC)
RAL code	7035
Colour	Light grey

**Equipment**

Has earthing terminal block	No
Has mounting plate	No

**Safety**

Protection class	Isolation class II
Impact resistance IK	IK08
Ingress Protection (IP) class	IP65
Locking type	3-Side 7 mm
Glow wire test	850 °C

**Sustainability**

RoHS conform	Yes
--------------	-----