



WMPS3PILOCK

3 Pole Isolator Switch Locking Plate

Technical Features

Electric current	
Switching current	10 A
Installation, mounting	
Mounting on	Flush mounting Surface mounting
Voltage	
Rated voltage	250 V
Materials	
Colour	White
Surface finish	Glossy
Material	Urea formaldehyde
Treatment	Untreated
Identification	
Assembly arrangement	Basic element with full cover plate
Connectivity	
Mounting type	Screw mounting
Controls and indicators	
Number of buttons	1
Dimensions	
Dimensions	86 x 86 mm
Built-in depth	13.10 mm
Safety	
Ingress Protection (IP) class	IP20
Architecture	
Control/operation element	Single rocker
Electric current	
Rated current	10 A
Texts	
Lighting	Without lighting (cannot be illuminated)
Switch mode	3-pole
Sustainability	
Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes