



FD32DN

Enclosure, NewVegaD, 600x550x193mm, 72 modules, surface-mounted, distribution

### Technical Features

#### Voltage

Nominal voltage	230 - 400 V
-----------------	-------------

#### Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

#### Electric current

Rated current	160 A
---------------	-------

#### Equipment

Number of rails	3
Number of rows	3
With lock	No
Has neutral terminal block	No

#### Capacity

Number of modules	72
-------------------	----

#### Dimensions

Height	600 mm
Width	550 mm
Depth	193 mm

#### Cover, door

Number of cabinet doors	0
Number of locks	0

#### Dimensions

Number of width units	24
-----------------------	----

#### Cover, door

Door/cover is transparent	No
---------------------------	----

#### Connection

Number of conduit inlets	4
--------------------------	---

#### Materials

Material	Metal Plastic
RAL code	9010
Colour	Pure white

#### Equipment

Has earthing terminal block	Yes
Has mounting plate	No

#### Safety

Protection class	Isolation class II
Impact resistance IK	IK07
Ingress Protection (IP) class	IP30
Locking type	Without lock

#### Sustainability

RoHS conform	Yes
--------------	-----