



FD32AN

Enclosure, NewVegaD, 600x550x193mm, 72 modules, surface-mounted, to complete

**Technical Features**

**Voltage**

Nominal voltage	230 - 400 V
-----------------	-------------

**Installation, mounting**

Suitable for outdoor usage	No
Mounting on	Surface mounting

**Electric current**

Rated current	160 A
---------------	-------

**Equipment**

Number of rails	1
Number of rows	3
With lock	No
Has neutral terminal block	No

**Capacity**

Number of modules	72
-------------------	----

**Dimensions**

Height	600 mm
Width	550 mm
Depth	193 mm

**Cover, door**

Number of cabinet doors	0
-------------------------	---

**Dimensions**

Number of width units	24
-----------------------	----

**Cover, door**

Door/cover is transparent	No
---------------------------	----

**Connection**

Number of conduit inlets	4
--------------------------	---

**Materials**

Material	Metal Plastic
RAL code	9010
Colour	Pure white

**Equipment**

Has earthing terminal block	Yes
Has mounting plate	No

**Safety**

Protection class	Isolation class II
Ingress Protection (IP) class	IP30
Locking type	Without lock

**Sustainability**

RoHS conform	Yes
--------------	-----