



FD32AN

Enclosure, NewVegaD, 600x550x193mm, 72 modules, surface-mounted, to complete

Technical Features

Voltage

Nominal voltage	230 - 400 V
-----------------	-------------

Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

Electric current

Rated current	160 A
---------------	-------

Equipment

Number of rails	1
Number of rows	3
With lock	No
Has neutral terminal block	No

Capacity

Number of modules	72
-------------------	----

Dimensions

Height	600 mm
Width	550 mm
Depth	193 mm

Cover, door

Number of cabinet doors	0
-------------------------	---

Dimensions

Number of width units	24
-----------------------	----

Cover, door

Door/cover is transparent	No
---------------------------	----

Connection

Number of conduit inlets	4
--------------------------	---

Materials

Material	Metal Plastic
RAL code	9010
Colour	Pure white

Equipment

Has earthing terminal block	Yes
Has mounting plate	No

Safety

Protection class	Isolation class II
Ingress Protection (IP) class	IP30
Locking type	Without lock

Sustainability

RoHS conform	Yes
--------------	-----