


75441171



**Thermostat with push-button interface, K.5, aluminium**

**Technical Features**

**Electric current**

Bus current consumption data transfer	10 mA
---------------------------------------	-------

**Functions**

Parallel service possible	Yes
With local operation	Yes

**Materials**

Colour	Aluminium
RAL code	9006

**Dimensions**

Dimensions	70.80 x 70.80 mm
Built-in depth	22.90 mm
Built-in depth flush-mounted boxes	26 mm

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Use conditions**

Operating temperature	-5 - 45 °C
Energy efficiency class	IV (2%)

**Voltage**

Operating voltage over bus	21 - 32 V
----------------------------	-----------

**Texts**

Installation mode	Without spreader claws
-------------------	------------------------

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes