


75441173



Thermostat with push-button interface, K.5, stainless steel, lacquered

Technical Features

Electric current

Bus current consumption data transfer	10 mA
---------------------------------------	-------

Functions

Parallel service possible	Yes
With local operation	Yes

Materials

Colour	Stainless steel
RAL code	9022

Dimensions

Dimensions	70.80 x 70.80 mm
Built-in depth	22.90 mm
Built-in depth flush-mounted boxes	26 mm

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Use conditions

Operating temperature	-5 - 45 °C
Energy efficiency class	IV (2%)

Voltage

Operating voltage over bus	21 - 32 V
----------------------------	-----------

Texts

Installation mode	Without spreader claws
-------------------	------------------------

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes