



WMGS22RPSW

### 20A 2 Way Retractive Switch Polished Steel White Insert

#### Technical Features

##### Electric current

Switching current	20 A
-------------------	------

##### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

##### Voltage

Rated voltage	250 V
---------------	-------

##### Materials

Colour	Silver
Surface finish	Glossy
Material	Stainless steel

##### Identification

Assembly arrangement	Basic element with central cover plate
----------------------	--

##### Connectivity

Mounting type	Snap-on mounting
---------------	------------------

##### Controls and indicators

Number of buttons	1
-------------------	---

##### Dimensions

Dimensions	59 x 25 mm
Built-in depth	13.10 mm

##### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

##### Architecture

Control/operation element	Single rocker
---------------------------	---------------

##### Electric current

Rated current	20 A
---------------	------

##### Texts

Lighting	Without lighting (cannot be illuminated)
Switch mode	2-pole

##### Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes