



HIM304

**Modular change-over switch 3x40A**

**Technical Features**

**Voltage**

Rated operational voltage U <sub>e</sub>	380 - 415 V
Rated insulation voltage U <sub>i</sub>	800 V
Rated impulse withstand voltage U <sub>imp</sub>	8000 V

**Electric current**

Rated current	40 A
Rated short-time withstand current I <sub>cw</sub> IEC 60947	1.26 kA
Rated conditional short-circuit current I <sub>cc</sub> with gI-gG fuses	50 kA

**Power**

Rated operational power under 400 V AC AC1	26000 W
--	---------

**Architecture**

Number of poles	3
Control/operation element	Short rotary handle
Type of pole	3P

**Dimensions**

Height	93.5 mm
Width	97.5 mm
Depth	110 mm

**Controls and indicators**

Motor drive integrated	No
------------------------	----

**Cover, door**

Interlockable	Yes
---------------	-----

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Capacity**

Number of modules	6
-------------------	---

**Power**

Total power loss under I <sub>N</sub>	2.70 W
---------------------------------------	--------

**Use conditions**

Operating temperature	-20 - 70 °C
-----------------------	-------------

**Connection**

Cross-section flexible conductor	1.5 - 16 mm <sup>2</sup>
Cross-section rigid conductor	1.5 - 16 mm <sup>2</sup>

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes