



WPPS32

**10AX 3 Gang 2 Way Wall Switch & Back Box with Knockouts**

**Technical Features**

**Electric current**

Switching current 10 A

**Installation, mounting**

Mounting on Flush mounting

**Voltage**

Rated voltage 250 V

**Materials**

Colour Grey

Surface finish Glossy

Material Steel

Treatment Epoxy

**Identification**

Assembly arrangement Basic element with complete housing

**Connectivity**

Mounting type Screw mounting

**Controls and indicators**

Number of buttons 3

**Dimensions**

Dimensions 86 x 86 mm

Built-in depth 0 mm

**Safety**

Ingress Protection (IP) class IP20

**Architecture**

Control/operation element Triple rocker

**Electric current**

Rated current 10 A

**Texts**

Installation mode For flush-mounted and hollow wall mounting

Lighting Without lighting (cannot be illuminated)

Switch mode 2-way

**Sustainability**

REACH-SVHC free Yes

RoHS conform Yes