



JG220U

IP66 20A 3P SW NEUTRAL UTILITY ISOLATOR

Technical Features

Architecture

Number of poles	4
Type of pole	3P+N

Electric current

Rated current	20 A
Acceptable current rating AC21 category A	20 A
Acceptable current rating AC22 category A	20 A

Voltage

Rated operational voltage Ue	380 - 440 V
Rated insulation voltage Ui	440 V

Installation, mounting

Nominal tightening torque	2 - 2 Nm
---------------------------	----------

Dimensions

Height	170 mm
Width	84 mm
Depth	87 mm

Safety

Ingress Protection (IP) class	IP66
-------------------------------	------

Use conditions

Operating temperature	-5 - 40 °C
-----------------------	------------

Connection

Cross-section rigid conductor	2.5 - 4 mm ²
-------------------------------	-------------------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes