



16246084

Rocker with orange lense and imprint "O", Q.x, aluminium velvety, lacquered

Technical Features

Architecture

Control/operation element	Single rocker
---------------------------	---------------

Materials

Colour	Aluminium
RAL code	9006
Surface finish	Velvety
Material	Duroplastic
Treatment	Varnished

Dimensions

Height	58 mm
Width	58 mm
Depth	22.50 mm

Connectivity

Mounting type	Clamp mounting
---------------	----------------

Equipment

Monitoring window/light outlet	Yes
--------------------------------	-----

Accessories

Has labelling field	No
---------------------	----

Safety

Ingress Protection (IP) class	IP20
Impact resistance IK	IK02
Usable in higher IP class	IP44 in combination with sealing set

Texts

Imprint	With imprint "O"
Installation mode	Clamp fastening
Lighting	For lighting and monitoring circuit
Push button	Also for KNX applications: group push-button, 1-gang
Rocker switch/rocker push-button	For multi-pole rocker switches

Suitable for

Q.x	
-----	--

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes