



16246089

**Rocker imprint "0", orangelens, Q.x, p. white velvety**

#### Technical Features

##### Architecture

Control/operation element	Single rocker
---------------------------	---------------

##### Materials

Colour	Polar white
RAL code	9010
Surface finish	Velvety
Material	Duroplastic
Treatment	Untreated

##### Dimensions

Height	58 mm
Width	58 mm
Depth	22.50 mm

##### Connectivity

Mounting type	Clamp mounting
---------------	----------------

##### Equipment

Monitoring window/light outlet	Yes
--------------------------------	-----

##### Accessories

Has labelling field	No
---------------------	----

##### Safety

Ingress Protection (IP) class	IP20
Impact resistance IK	IK02
Usable in higher IP class	IP44 in combination with sealing set

##### Texts

Imprint	With imprint "0"
Installation mode	Clamp fastening
Lighting	For lighting and monitoring circuit
Push button	Also for KNX applications: group push-button, 1-gang
Rocker switch/rocker push-button	For multi-pole rocker switches

##### Suitable for

Q.x	
-----	--

##### Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes