



75441273



IP20



KNX object thermostat, intg bus coupl. unit, KNX-K.5, steel, metal matt finish

Technical Features

Electric current

Bus current consumption data transfer 7.50 mA

Functions

Parallel service possible No

With local operation No

Materials

Colour Stainless steel

RAL code 9022

Dimensions

Dimensions 70.80 x 70.80 mm

Built-in depth 22.70 mm

Built-in depth flush-mounted boxes 26 mm

Safety

Ingress Protection (IP) class IP20

Use conditions

Operating temperature -5 - 45 °C

Energy efficiency class IV (2%)

Voltage

Operating voltage over bus 21 - 32 V

Texts

Installation mode Without spreader claws

Sustainability

REACH-SVHC free Yes

RoHS conform Yes