



KD304M

Insulated busbar for 4 motor starters 3P 63A fork 10mm²

Technical Features

Electric current

Rated current 63 A

Architecture

Number of poles 3

Dimensions

Length 176 mm

Voltage

Rated impulse withstand voltage Uimp 4500 V

Rated operational voltage Ue 230 - 400 V

Connection

Cross-section rigid conductor 10 mm²

Connector/plug type Phase busbar with fork

Use conditions

Operating temperature -25 - 55 °C

Capacity

Number of modules 10

Sustainability

RoHS conform Yes