



KD304M

Insulated busbar for 4 motor starters 3P 63A fork 10mm<sup>2</sup>

Technical Features

Electric current

Rated current	63 A
---------------	------

Architecture

Number of poles	3
-----------------	---

Dimensions

Length	176 mm
--------	--------

Voltage

Rated impulse withstand voltage U <sub>imp</sub>	4500 V
Rated operational voltage U <sub>e</sub>	230 - 400 V

Connection

Cross-section rigid conductor	10 mm <sup>2</sup>
Connector/plug type	Phase busbar with fork

Use conditions

Operating temperature	-25 - 55 °C
-----------------------	-------------

Capacity

Number of modules	10
-------------------	----

Sustainability

RoHS conform	Yes
--------------	-----