




75441279



IP20



**KNX object thermostat, intg bus coupling unit, KNX - K.1, p. white glossy**

**Technical Features**

**Electric current**

|                                       |         |
|---------------------------------------|---------|
| Bus current consumption data transfer | 7.50 mA |
|---------------------------------------|---------|

**Functions**

|                           |    |
|---------------------------|----|
| Parallel service possible | No |
| With local operation      | No |

**Materials**

|          |             |
|----------|-------------|
| Colour   | Polar white |
| RAL code | 9010        |

**Dimensions**

|                                    |                  |
|------------------------------------|------------------|
| Dimensions                         | 70.80 x 70.80 mm |
| Built-in depth                     | 22.70 mm         |
| Built-in depth flush-mounted boxes | 26 mm            |

**Safety**

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

**Use conditions**

|                         |            |
|-------------------------|------------|
| Operating temperature   | -5 - 45 °C |
| Energy efficiency class | IV (2%)    |

**Voltage**

|                            |           |
|----------------------------|-----------|
| Operating voltage over bus | 21 - 32 V |
|----------------------------|-----------|

**Texts**

|                   |                        |
|-------------------|------------------------|
| Installation mode | Without spreader claws |
|-------------------|------------------------|

**Sustainability**

|                 |     |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |