



KD303M

**Insulated busbar for 3 motor starters 3P 63A fork 10mm<sup>2</sup>**

**Technical Features**

**Electric current**

Rated current 63 A

**Architecture**

Number of poles 3

**Dimensions**

Length 132 mm

**Voltage**

Rated impulse withstand voltage Uimp 4500 V

Rated operational voltage Ue 230 - 400 V

**Connection**

Cross-section rigid conductor 10 mm<sup>2</sup>

Connector/plug type Phase busbar with fork

**Use conditions**

Operating temperature -25 - 55 °C

**Capacity**

Number of modules 7.50

**Sustainability**

RoHS conform Yes