



VD108TT

Sm.distr.,VD/IC²,surface,1row,8M,IP40,MS-terminals,N+PE,AUS,transparent door

Technical Features

Voltage

Nominal voltage	400 - 400 V
-----------------	-------------

Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

Electric current

Rated current	63 A
---------------	------

Equipment

Number of rails	1
Number of rows	1
Number of section in width	1
With lock	No
Has neutral terminal block	Yes

Capacity

Number of modules	8
-------------------	---

Functions

With conduit inlets	Yes
---------------------	-----

Dimensions

Height	170 mm
Width	170.50 mm
Depth	91 mm

Cover, door

Number of cabinet doors	1
Number of locks	0

Dimensions

Number of width units	8
-----------------------	---

Cover, door

Door/cover is transparent	Yes
---------------------------	-----

Materials

Material	Plastic
RAL code	9010
Colour	Pure white

Equipment

Has earthing terminal block	Yes
Has mounting plate	No

Materials

Ultraviolet-resistant	No
-----------------------	----

Safety

Protection class	Isolation class II
Ingress Protection (IP) class	IP40
Locking type	Snap on lock Without lock
Glow wire test	650 °C

Sustainability

RoHS conform	Yes
--------------	-----