



85656231



**KNX radio wall-transmitter 2gang flat quicklink, R.1/R.3, black glossy**

**Technical Features**

**Settings**

Supported configuration mode quicklink

**Voltage**

Operating voltage 3 - 3 V

**Equipment**

Number of channels 4

Transmitter duty cycle 1 %

**Connectivity**

Radio protocol KNX Radio

Receiver category 2

**Use conditions**

Operating temperature -5 - 45 °C

**Dimensions**

Assembling height 14 mm

**Materials**

Colour Black

Material Thermoplastic

**Safety**

Ingress Protection (IP) class IP20

**Texts**

Function Easy additional functions: +6 scenes, on/off operating mode, 1 up/down button control  
Reset function (to factory setting)

Protection With dismantling protection

Installation mode For flat surface mounting and extension of combinations

**Sustainability**

RoHS conform Yes