



WGCT2RJ

### RJ11 outlet (2mod)

#### Technical Features

##### Frequency

Transmission bandwidth	0-100 MHz
------------------------	-----------

##### Equipment

With transparent label holder	No
-------------------------------	----

Number of outputs	2
-------------------	---

##### Use conditions

Operating temperature	-20 - 45 °C
-----------------------	-------------

##### Equipment

With hinged lid	No
-----------------	----

##### Materials

Colour	White
--------	-------

##### Connection

Connector/plug type	RJ45
---------------------	------

##### Materials

Material	Polycarbonate (PC)
----------	--------------------

##### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

##### Voltage

Rated voltage	0 V
---------------	-----

##### Electric current

Rated current	0 A
---------------	-----

##### Dimensions

Built-in depth	27 mm
----------------	-------

##### Texts

Supporting plate/supporting ring	With supporting plate
----------------------------------	-----------------------

##### Sustainability

RoHS conform	Yes
--------------	-----