



SVN461

**Impulse 2NO Pushbutton + green Indicator light 12/48V**

**Technical Features**

**Equipment**

|                        |     |
|------------------------|-----|
| Number of INV contacts | 0   |
| Number of NC contacts  | 0   |
| Number of NO contacts  | 2   |
| With signal lamp       | Yes |

**Electric current**

|                           |      |
|---------------------------|------|
| Momentary contact current | 16 A |
| Rated current             | 16 A |

**Capacity**

|                   |   |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

**Dimensions**

|        |          |
|--------|----------|
| Height | 83 mm    |
| Width  | 17.50 mm |
| Depth  | 66 mm    |

**Voltage**

|                              |           |
|------------------------------|-----------|
| Rated insulation voltage Ui  | 250 V     |
| Rated operational voltage Ue | 12 - 48 V |

**Sustainability**

|                 |     |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |

**Illustrations | Drawings**

