




85656282



**KNX radio wall-transmitter 2gang flat quicklink, S.1, white glossy**

**Technical Features**

**Settings**

|                              |           |
|------------------------------|-----------|
| Supported configuration mode | quicklink |
|------------------------------|-----------|

**Voltage**

|                   |         |
|-------------------|---------|
| Operating voltage | 3 - 3 V |
|-------------------|---------|

**Equipment**

|                        |     |
|------------------------|-----|
| Number of channels     | 4   |
| Transmitter duty cycle | 1 % |

**Connectivity**

|                   |           |
|-------------------|-----------|
| Radio protocol    | KNX Radio |
| Receiver category | 2         |

**Use conditions**

|                       |            |
|-----------------------|------------|
| Operating temperature | -5 - 45 °C |
|-----------------------|------------|

**Dimensions**

|                   |       |
|-------------------|-------|
| Assembling height | 14 mm |
|-------------------|-------|

**Materials**

|          |               |
|----------|---------------|
| Colour   | White         |
| Material | Thermoplastic |

**Safety**

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

**Texts**

|                   |                                                                                                                              |
|-------------------|------------------------------------------------------------------------------------------------------------------------------|
| Function          | Easy additional functions: +6 scenes, on/off operating mode, 1 up/down button control<br>Reset function (to factory setting) |
| Protection        | With dismantling protection                                                                                                  |
| Installation mode | For flat surface mounting and extension of combinations                                                                      |

**Sustainability**

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|