



29516084



**LED signal light RGB Q.1/Q.3 alu velvety, lacquered**

**Technical Features**

**Voltage**

Rated voltage	230 V
---------------	-------

**Power**

Power absorbed	2 W
----------------	-----

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Lighting**

Type of lamp	LED
--------------	-----

**Materials**

Colour	Aluminium
RAL code	9006
Surface finish	Velvety
Material	Metal Plastic
Treatment	Varnished

**Dimensions**

Height	70 mm
Width	70 mm
Depth	50 mm

**Connection**

Conductor cross-section	2.50 - 2.50 mm <sup>2</sup>
-------------------------	-----------------------------

**Connectivity**

Mounting type	Claw mounting Screw connection
---------------	-----------------------------------

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Texts**

Lighting	Light colours cold white, warm white, blue, orange, red, green, purple (magenta) and colour sequence callable via push-button Colour sequence can be stopped at any position via the push-button.
Labelling	Foils with imprint of symbols insertable
Imprint	Without imprint