



WBQSA1

**FIN Architrave 1 gang**

**Technical Features**

**Installation, mounting**

Mounting on	Flush mounting
-------------	----------------

**Voltage**

Rated voltage	250 V
---------------	-------

**Frequency**

Frequency	50 - 50 Hz
-----------	------------

**Materials**

Colour	White
--------	-------

**Identification**

Assembly arrangement	Basic element with full cover plate
----------------------	-------------------------------------

**Connectivity**

Mounting type	Screw mounting
---------------	----------------

**Controls and indicators**

Number of buttons	1
-------------------	---

**Safety**

Ingress Protection (IP) class	IP2X
-------------------------------	------

**Electric current**

Rated current	16 A
---------------	------

**Texts**

Installation mode	For screw fastening
Type of connection	With screw terminals
Lighting	Without lighting (cannot be illuminated)
Switch mode	2-way, with loop terminal

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes