



WBQSA1

FIN Architrave 1 gang

Technical Features

Installation, mounting

Mounting on Flush mounting

Voltage

Rated voltage 250 V

Frequency

Frequency 50 - 50 Hz

Materials

Colour White

Identification

Assembly arrangement Basic element with full cover plate

Connectivity

Mounting type Screw mounting

Controls and indicators

Number of buttons 1

Safety

Ingress Protection (IP) class IP2X

Electric current

Rated current 16 A

Texts

Installation mode For screw fastening

Type of connection With screw terminals

Lighting Without lighting (cannot be illuminated)

Switch mode 2-way, with loop terminal

Sustainability

Halogen free Yes

REACH-SVHC free Yes

RoHS conform Yes