



WBQSA3

FIN Architrave 3 gang

Technical Features

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Voltage

Rated voltage	250 V
---------------	-------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Materials

Colour	White
--------	-------

Identification

Assembly arrangement	Basic element with full cover plate
----------------------	-------------------------------------

Connectivity

Mounting type	Screw mounting
---------------	----------------

Controls and indicators

Number of buttons	3
-------------------	---

Safety

Ingress Protection (IP) class	IP2X
-------------------------------	------

Electric current

Rated current	16 A
---------------	------

Texts

Installation mode	For screw fastening
-------------------	---------------------

Type of connection	With screw terminals
--------------------	----------------------

Lighting	Without lighting (cannot be illuminated)
----------	--

Switch mode	2-way, with loop terminal
-------------	---------------------------

Sustainability

Halogen free	Yes
--------------	-----

REACH-SVHC free	Yes
-----------------	-----

RoHS conform	Yes
--------------	-----