



WRDP84PSB

**20A Double Pole Switch Polished Steel Black Insert**

**Technical Features**

**Installation, mounting**

Mounting on Flush mounting

**Voltage**

Rated voltage 250 V

**Materials**

Colour Silver

Surface finish Glossy

Material Stainless steel

**Identification**

Assembly arrangement Basic element with full cover plate

**Connectivity**

Mounting type Screw mounting

**Controls and indicators**

Number of buttons 1

**Dimensions**

Dimensions 86 x 86 mm

Built-in depth 20 mm

**Safety**

Ingress Protection (IP) class IP20

**Architecture**

Control/operation element Single rocker

**Electric current**

Rated current 20 A

**Texts**

Lighting Without lighting (cannot be illuminated)

Switch mode 2-pole

**Sustainability**

Halogen free Yes

REACH-SVHC free Yes

RoHS conform Yes