



936552524

Series switch, com input term, Integro - Design Flow/Pure, stain steel m, lacq

Technical Features

Electric current

Switching current 10 A

Voltage

Rated voltage 250 V

Materials

Colour Stainless steel

RAL code 9022

Surface finish Matt

Material Stainless steel
Thermoplastic

Treatment Varnished

Identification

Assembly arrangement Basic element with central cover plate

Connectivity

Mounting type Built in installation
Screw mounting

Controls and indicators

Number of buttons 2

Dimensions

Dimensions 55.50 x 55.50 mm

Built-in depth 10 mm

Built-in depth flush-mounted boxes 13 mm

Safety

Ingress Protection (IP) class IP20

Architecture

Control/operation element Double rocker

Electric current

Rated current 10 A

Texts

Installation mode For screw fastening

Type of connection With screw terminals

Lighting Without lighting (cannot be illuminated)

Switch mode Series

Sustainability

RoHS conform Yes