



WBQP1S

FIN Single GPO 10A

Technical Features

Electric current

| | |
|---------------|------|
| Rated current | 10 A |
|---------------|------|

Frequency

| | |
|-----------|------------|
| Frequency | 50 - 50 Hz |
|-----------|------------|

Materials

| | |
|--------|-------|
| Colour | White |
|--------|-------|

Installation, mounting

| | |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

Connectivity

| | |
|--------------------|----------------|
| Type of connection | Screw terminal |
|--------------------|----------------|

| | |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

Equipment

| | |
|-----------------------------------|---------------------------------|
| Connector/plug type socket outlet | Australian standard AS/NZS 3112 |
|-----------------------------------|---------------------------------|

| | |
|------------------------|----|
| Rotated central insert | No |
|------------------------|----|

| | |
|-----------------|----|
| With hinged lid | No |
|-----------------|----|

Accessories

| | |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

Capacity

| | |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP2X |
|-------------------------------|------|

Functions

| | |
|---------------------------|----|
| With orientation lighting | No |
|---------------------------|----|

| | |
|------------------------|----|
| With function lighting | No |
|------------------------|----|

Texts

| | |
|---------|-----------------|
| Imprint | Without imprint |
|---------|-----------------|

| | |
|-------|------------------|
| Cover | Full cover plate |
|-------|------------------|

| | |
|--------------------|----------------------|
| Type of connection | With screw terminals |
|--------------------|----------------------|

Suitable for

| | |
|---------|--|
| finesse | |
|---------|--|

Sustainability

| | |
|--------------|-----|
| Halogen free | Yes |
|--------------|-----|

| | |
|-----------------|-----|
| REACH-SVHC free | Yes |
|-----------------|-----|

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|