



WBQP2S

FIN DGPO 10A

Technical Features

Electric current

Rated current 10 A

Frequency

Frequency 50 - 50 Hz

Materials

Colour White
Surface finish Glossy
Material Polycarbonate (PC)
Thermoplastic

Dimensions

Height 82 mm
Width 120 mm

Installation, mounting

Mounting on Flush mounting

Connectivity

Type of connection Screw terminal
Mounting type Screw mounting

Equipment

Connector/plug type socket outlet Australian standard AS/NZS 3112
Rotated central insert No
With hinged lid No
With round protective earth pin No
With signal lamp No

Accessories

Has labelling field No

Capacity

Number of modules 2

Safety

Impact resistance IK IK08
Ingress Protection (IP) class IP20

Functions

With orientation lighting No
With function lighting No

Identification

With imprint No

Texts

Cover Full cover plate
Protection Enhanced contact protection
Type of connection With screw terminals

Suitable for

finesse

Sustainability

REACH-SVHC free Yes
RoHS conform Yes