



FL176A

Steel enclosure, Orion.Plus, glazed door 950x600x300 mm

Technical Features

Dimensions

| | |
|-----------------------|---------|
| Height | 950 mm |
| Width | 600 mm |
| Depth | 300 mm |
| Thickness of sidewall | 1.20 mm |

Safety

| | |
|-------------------------------|-------------------------|
| Ingress Protection (IP) class | IP65 |
| Protection class | Isolation class I |
| Locking type | 3-Side 7 mm Key lock |
| Impact resistance IK | IK10 |

Equipment

| | |
|---------------------------------|---|
| Number of flange plate openings | 2 |
|---------------------------------|---|

Installation, mounting

| | |
|----------------------------|---------------|
| Mounting on | Wall mounting |
| Suitable for outdoor usage | No |

Materials

| | |
|-----------|---------------|
| Colour | Light grey |
| RAL code | 7035 |
| Treatment | Powder coated |
| Material | Steel |

Equipment

| | |
|----------------|---|
| Number of rows | 6 |
|----------------|---|

Cover, door

| | |
|---------------------------|-------------|
| Number of cabinet doors | 1 |
| Number of locks | 2 |
| Door/cover is transparent | Yes |
| Cabinet door type | Single door |

Electric current

| | |
|---------------|-------|
| Rated current | 250 A |
|---------------|-------|

Sustainability

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|