



FL172A

Steel enclosure, Orion.Plus, glazed door 800x500x250 mm

### Technical Features

#### Dimensions

Height	800 mm
Width	500 mm
Depth	250 mm
Thickness of sidewall	1.20 mm

#### Safety

Ingress Protection (IP) class	IP65
Protection class	Isolation class I
Locking type	3-Side 7 mm Key lock
Impact resistance IK	IK10

#### Equipment

Number of flange plate openings	2
---------------------------------	---

#### Installation, mounting

Mounting on	Wall mounting
Suitable for outdoor usage	No

#### Materials

Colour	Light grey
RAL code	7035
Treatment	Powder coated
Material	Steel

#### Equipment

Number of rows	5
----------------	---

#### Cover, door

Number of cabinet doors	1
Door/cover is transparent	Yes

#### Electric current

Rated current	250 A
---------------	-------

#### Sustainability

RoHS conform	Yes
--------------	-----