



FL173A

**Steel enclosure, Orion.Plus, glazed door 800x600x250 mm**

**Technical Features**

**Dimensions**

|                       |         |
|-----------------------|---------|
| Height                | 800 mm  |
| Width                 | 600 mm  |
| Depth                 | 250 mm  |
| Thickness of sidewall | 1.20 mm |

**Safety**

|                               |                         |
|-------------------------------|-------------------------|
| Ingress Protection (IP) class | IP65                    |
| Protection class              | Isolation class I       |
| Locking type                  | 3-Side 7 mm<br>Key lock |
| Impact resistance IK          | IK10                    |

**Equipment**

|                                 |   |
|---------------------------------|---|
| Number of flange plate openings | 2 |
|---------------------------------|---|

**Installation, mounting**

|                            |               |
|----------------------------|---------------|
| Mounting on                | Wall mounting |
| Suitable for outdoor usage | No            |

**Materials**

|           |               |
|-----------|---------------|
| Colour    | Light grey    |
| RAL code  | 7035          |
| Treatment | Powder coated |
| Material  | Steel         |

**Equipment**

|                |   |
|----------------|---|
| Number of rows | 5 |
|----------------|---|

**Cover, door**

|                           |     |
|---------------------------|-----|
| Number of cabinet doors   | 1   |
| Number of locks           | 2   |
| Door/cover is transparent | Yes |

**Electric current**

|               |       |
|---------------|-------|
| Rated current | 250 A |
|---------------|-------|

**Sustainability**

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|