



FL173A

### Steel enclosure, Orion.Plus, glazed door 800x600x250 mm

#### Technical Features

##### Dimensions

Height	800 mm
Width	600 mm
Depth	250 mm
Thickness of sidewall	1.20 mm

##### Safety

Ingress Protection (IP) class	IP65
Protection class	Isolation class I
Locking type	3-Side 7 mm Key lock
Impact resistance IK	IK10

##### Equipment

Number of flange plate openings	2
---------------------------------	---

##### Installation, mounting

Mounting on	Wall mounting
Suitable for outdoor usage	No

##### Materials

Colour	Light grey
RAL code	7035
Treatment	Powder coated
Material	Steel

##### Equipment

Number of rows	5
----------------	---

##### Cover, door

Number of cabinet doors	1
Number of locks	2
Door/cover is transparent	Yes

##### Electric current

Rated current	250 A
---------------	-------

##### Sustainability

RoHS conform	Yes
--------------	-----