




VF318PZD

**Small distributor,golf,flush,MM,54M,3row,white door,slotted**

### Technical Features

#### Voltage

|                 |             |
|-----------------|-------------|
| Nominal voltage | 400 - 400 V |
|-----------------|-------------|

#### Installation, mounting

|                            |                |
|----------------------------|----------------|
| Suitable for outdoor usage | No             |
| Mounting on                | Flush mounting |

#### Equipment

|                            |    |
|----------------------------|----|
| Number of rails            | 3  |
| Number of rows             | 3  |
| Number of section in width | 1  |
| With lock                  | No |
| Has neutral terminal block | No |

#### Capacity

|                   |    |
|-------------------|----|
| Number of modules | 54 |
|-------------------|----|

#### Functions

|                     |     |
|---------------------|-----|
| With conduit inlets | Yes |
|---------------------|-----|

#### Dimensions

|                |          |
|----------------|----------|
| Height         | 543 mm   |
| Width          | 460 mm   |
| Depth          | 97.50 mm |
| Built-in width | 426 mm   |

#### Cover, door

|                         |   |
|-------------------------|---|
| Number of cabinet doors | 1 |
|-------------------------|---|

#### Dimensions

|                |       |
|----------------|-------|
| Built-in depth | 72 mm |
|----------------|-------|

#### Cover, door

|                 |   |
|-----------------|---|
| Number of locks | 0 |
|-----------------|---|

#### Dimensions

|                       |    |
|-----------------------|----|
| Number of width units | 18 |
|-----------------------|----|

#### Cover, door

|                           |    |
|---------------------------|----|
| Door/cover is transparent | No |
|---------------------------|----|

#### Materials

|          |            |
|----------|------------|
| Material | Plastic    |
| RAL code | 9010       |
| Colour   | Pure white |

#### Equipment

|                             |     |
|-----------------------------|-----|
| Has earthing terminal block | No  |
| Has mounting plate          | Yes |

#### Safety

|                      |                              |
|----------------------|------------------------------|
| Impact resistance IK | IK07                         |
| Locking type         | Snap on lock<br>Without lock |
| Glow wire test       | 650 °C                       |

#### Sustainability

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|